


C125 (GT) 3-way (hot, cold, drink) tap water faucet




The kitchen faucet model C125 (GT) is intended for use as a water tap and a tap for drinking water with Aquaphor ater purifiers, which are built into the water supply system.

Specifications

Maximum working water pressure	0.63 MPa (6.5 at)
Cold water temperature	from +4 to +38 °C
Hot water temperature	before 70 °C
Filtered water temperature	from +4 to +38 °C
Complete faucet weight	2.12 kg

Contents of delivery

Name	Quantity
Faucet assembly	1 pc
Flexible hoses for cold and hot water (43, 44), L=600 mm, G1/2"	2 pcs
Triangle base (4)	1 pc
Allen keys (45)	3 pcs
Manual	1 pc
Packing kit	1 pc




- 9. A tube
- 10. Sealing ring
- 11. Base ring
- 12. Faucet body
- 13. Sealing ring
- 14. Connecting sleeve
- 15. Small cartridge
- 16. Silicone ring
- 17. Transparent ring
- 18. Silicone ring
- 19. Stuffing box


- 22. Plastic ring (gray)
- 23. Handle cover
- 24. Screw
- 25. Sealing ring
- 26. Handle
- 27. Cartridge
- 28. Screw
- 29. Decorative nut
- 30. Screw M5x4
- 31. Handle cover
- 32. Handle

- 35. Plastic ring
- 36. Sealing ring
- 37. Sealing ring
- 38. Rubber ring
- 39. Spout
- 40. Aerator
- 41. Silicone ring
- 42. Rubber ring
- 43, 44. Flexible hoses for hot, cold water
- 45. Allen keys

2. The location of the holes for connecting the eyeliner and the threaded rod



Hole for flexible hot water connection



Installation of the faucet

Please read this manual carefully before installing the faucet.

- 1. Drill a hole with a diameter of 35 mm in the sink (countertop).
- Screw the flexible hoses (43, 44) and the drinking water supply (5) into the corresponding holes located in the base
 of the faucet body (12), follow the instructions in Fig. 2. to connect to Aquaphor water purifiers, use the drinking
 water supply (5) (see the instruction manual for your water purifier). Additional accessories may be required to
 connect the faucet to other water purifiers (see your water purifier's instruction manual).
- 3. Insert the faucet assembly into the opening of the sink, with the base (4) placed on top of the sink.
- 4. Place the rubber ring (3) and the steel nut (2) on the faucet from the bottom of the sink and screw on the nut (1).
- 5. Connect the pipe from the water purifier to the supply (5), tighten the connection with the nut (6) (Fig. 1).
- 6. Place the faucet in a comfortable position and finally tighten the nut (1).

Recommendations for use and care

- Wipe the product regularly with a soft cloth dampened with soapy water.
- Do not use abrasive products, caustic chemicals or solvents to clean the faucet surfaces.
- When using the product in areas with hard water or water with a high mineral content, careful care of the surface of the faucet is recommended to prevent salt deposits.
- · Clean the aerator regularly.

Disposal is carried out in accordance with environmental, sanitary and other requirements established by national standards in the field of environmental protection and ensuring the sanitary and epidemiological welfare of the population.

Service life and warranty

The service life of the faucet is 5 years from the date of sale. At the end of its service life, the faucet must be replaced. Operation of the faucet after the end of its service life may cause damage to the property of the consumer or other persons.

The shelf life of the faucet before the start of operation is no more than 3 years from the date of production specified in this manual, at a temperature of +5 to 38 °C without breaking the packaging.

The warranty period for the operation of the faucet is 1 year from the date of sale.

The product is not subject to warranty service in the following cases:

- when operating in violation of the requirements specified in this manual;
- in case of violation of the installation and installation rules set forth in this manual;
- if this instruction manual with the dates of production and / or sale is lost and there are no other ways to determine the service life of the product.

The faucet is made of lead-free materials.

Certified by IAPMO RESEARCH AND TASTING, INC. File No. N-9649.

Manufacturer: Foshan Shunde Gettai Sanitary Products Co.,Ltd, Block B, No.12 Huatian Road, Huakou, Ronggui Town, Shun-de District, Foshan City, Guangdong Province, China.

The manufacturer reserves the right to make improvements to the design of the faucet without reflecting them in the passport.



Date of production and quality control

GT2313-05-PH

Date of sale, shop stamp